SIZES IN STOCK READY TO SHIP

THOMAS MACHINERY HAS YOU COVERED!

PODO



SK PODO, round Ø 5 mm					
	Image	Part Product	Description	Grit	
		RT341PD-C100	XS-C Podo Cap 05080 - 100/Pack	Coarse	
	RPM: 7,000 - 10,000 (May RPM: 11,000)	RT341PD-M100	XS-M Podo Cap 05150 - 100/Pack	Medium	

SK PODO, round Ø 7 mm						
Image	Image Part Product Descrip		Grit			
	RT342PD-C100	S-C Podo Cap 07080 - 100/Pack	Coarse			
RPM: 7,000 - 10,000 (Max RPM: 11,000)	RT342PD-M100	S-M Podo Cap 07150 - 100/Pack	Medium			

Sk PODO, round Ø 10 mm				
	Image	Part Product	Description	Grit
		RT343PD-C100	M-C Podo Cap 10080 - 100/Pack	Coarse
		RT343PD-M100	M-M Podo Cap 10150 - 100/Pack	Medium

	SK PODO, round @ 13 mm				
	Image	Part Product	Description	Grit	
	RPM: 7,000 - 10,000 (Max RPM: 11,000)	RT344PD-C50	L-C Podo Cap 13080 - 50/Pack	Coarse	
		RT344PD-M50	L-M Podo Cap 13150 - 50/Pack	Medium	
		RT344PD-C100	L-C Podo Cap 13080 - 100/Pack	Coarse	
		RT344PD-M100	L-M Podo Cap 13150 - 100/Pack	Medium	

:	SK PODO, round Ø 16 n	nm		
	Image	Part Product	Description	Grit
	RPM: 7,000 - 10,000 (Max RPM: 11,000)	RT345PD-C25	XL-C Podo Cap 16080 - 25 /Pack	Coarse
		RT345PD-M25	XL-M Podo Cap 16150 - 25 /Pack	Medium
		RT345PD-C50	XL-C Podo Cap 16080 - 50 /Pack	Coarse
		RT345PD-M50	XL-M Podo Cap 16150 - 50/Pack	Medium
		RT345PD-C100	XL-C Podo Cap 16080 - 100 /Pack	Coarse
		RT345PD-M100	XL-M Podo Cap 16150 - 100/Pack	Medium

Precise - Exact Fit - Safe

THERMO

SK THERMO, round Ø 5 mm



Image	Part Product	Description Gri			
	RT341TH-C100	XS-C Thermo Cap 05080 - 100/Pack	Coarse		
RPM: 7,000 - 10,000 (Max RPM: 11,000)	RT341TH-M100	XS-M Thermo Cap 05150 - 100/Pack	Medium		

K THERMO, round Ø 7	' mm		
Image	Part Product	Description	Grit
460	RT342TH-C100	S-C Thermo Cap 07080 - 100/Pack	Coarse
RPM: 7,000 - 10,000 (Max RPM: 11,000)	RT342TH-M100	S-M Thermo Cap 07150 - 100/Pack	Medium

SK THERMO, round Ø 10 mm				
Image	Part Product	Description	Grit	
	RT343TH-C100	M-C Thermo Cap 10080 - 100/Pack	Coarse	
RPM: 7,000 - 10,000 (Max RPM: 11,000)	RT343TH-M100	M-M Thermo Cap 10150 - 100/Pack	Medium	

SK THERMO, round Ø 13 mm					
Image	Part Product	Description	Grit		
RPM: 7,000 - 10,000 (Max RPM: 11,000)	RT344TH-C50	L-C Thermo Cap 13080 - 50/Pack	Coarse		
	RT344TH-M50	L-M Thermo Cap 13150 - 50/Pack	Medium		
	RT344TH-C100	L-C Thermo Cap 13080 - 100/Pack	Coarse		
	RT344TH-M100	L-M Thermo Cap 13150 - 100/Pack	Medium		

SK THERMO, round Ø 16 mm				
Image	Part Product	Description	Grit	
	RT345TH-C25	XL-C Thermo Cap 16080 - 25 /Pack	Coarse	
Contract of the Contract of th	RT345TH-M25	XL-M Thermo Cap 16150 - 25 /Pack	Medium	
	RT345TH-C50	XL-C Thermo Cap 16080 - 50 /Pack	Coarse	
RPM: 7,000 - 10,000	RT345TH-M50	XL-M Thermo Cap 16150 - 50/Pack	Medium	
(Max RPM: 11,000)	RT345TH-C100	XL-C Thermo Cap 16080 - 100 /Pack	Coarse	
RT345TH-M1	RT345TH-M100	XL-M Thermo Cap 16150 - 100/Pack	Medium	









Treese Exactiff Date	IIIIage	Fait Floudet	Description	Recommended Speed / RF
The LUKAS abrasive cap holders provide a precise fit to both PODO		RT341-3/32	GT PODO 5 mm round XS	RPM: 7,000 - 10,000 (Max RPM: 11,000)
and THERMO abrasive caps and ensure high safety in medical foot care. During the treatment, the cap		RT342-3/32	GT PODO 7 mm round S	RPM: 7,000 - 10,000 (Max RPM: 11,000)
is held firmly in place on the holder. After use, it's quickly exchanged.		RT343-3/32	GT PODO 10 mm round M	RPM: 7,000 - 10,000 (Max RPM: 11,000)
All LUKAS GT PODO cap holders feature a stainless steel shaft.		RT344-3/32	GT PODO 13 mm round L	RPM: 7,000 - 10,000 (Max RPM: 11,000)
Holders are sold 5pcs / pack.			GT PODO 16 mm round	RPM: 7,000 - 10,000
		RT345-3/32	XL	(Max RPM: 11,000)



The world's first innovative colour change



PODIATRYINNOVATIONS

Explore the BIG world of Small Instruments



ENGINEERED SOLUTIONS - POWERED BY:



PRECISIO NTHE RIGHT TOOLS MATTER

► ROTATOOL BURRS TIAIN - AC-BLUE WEAR PROTECTION COATING

Quick removal of thick gryphotic nails and callus, treatment of orthosis silicones and hyperkeratosis.

Characteristics: Very high durability and removal rate, easy cleaning and longer service life, no heat development.



COARSE CROSS CUT Coarse shaping of nails,



MEDIUM CROSS CUT Removal of callus, designing of fungal infected nails, medium removal nails rate



FINE CROSS CUT Delicate treatment of the nail surface, nail wall and cuticle



► ROTATOOL BURRS PATENTED NEM

NEM - Quick removal of callus, smoothening and designing of fungal infected nails. Treatment of cuticle and nail fold. Recommended for diabetics.

Characteristics: Coarse and fine segments on one cutter, this means unmatched cutting performance together with smooth surfaces, very smooth running, long service life and especially gentle for the patient.



RT505-NEM RT512-NEM



















► ROTATOOL BURRS LSQ

Quick removal of thick grypotic nails and callus, treatment of orthesis silicones and hyperkerathosis, high removal rate.









Browse our complete selection online at: www.rotatool.com



Training for specific tools is available!

► ROTATOOL BURRS LGQ

LGO: Quick removal of thick gryphotic nails and callus treatment of orthesis silicones and hyperkerathosis, very high removal rate.









NEQ Ball Cutter Characteristics: All diameters have 8 blades, very sharp and effective. Treatment of corns and nail mycosis,

TREPHINE - Removal of corns and calluses, removal of cornea









► ROTATOOL BURRS XC / COARSE / MEDIUM

Are ideal for podiatry work to quickly reduce & smooth out unattractive nails.

Strong removal of wooden nails, super coarse removal rate, Coarse shaping of nails, coarse removal rate, Removal of callus, designing of fungal infected nails, medium removal rate. *These precise instruments are only to be used by trained Foot Care Professionals.



EXTRA COARSE CUT





removal of calluses.





MEDIUM CUT









ROTATOOL DIAMONDS

Work on calluses & corns more efficiently than with traditional files. Smaller diamonds help to bring bent nails back to form, eliminating pressure and improving shape. These tools also eliminate difficult corners & edges, and easily remove unwanted material from under the front of nails. (Different grits available.)



















RT476C

RT501NEQ 1.8 mm



RT476XC







► ROTATOOL DIAMONDS XPRT

Are ideal for podiatry work to quickly reduce & smooth out unattractive nails. They can also be used to clean heels and remove hard calluses. (Different grits available.)

























